

Datasheet revision 1.3 www.chipquik.com

# Liquid Flux Rosin Mildly Activated (RMA) in 10ml (0.34oz) Pen w/tip

# **Product Highlights**

High Solids Content

No-Clean

Alcohol-Based

Ideal for all rework, solder, and de-solder applications

**Excellent wetting** 

Easily cleaned with water or isopropyl alcohol (IPA)

Can be used with Leaded and Lead-Free applications

**RoHS 3 and REACH compliant** 



Flux Type: RMA Liquid (for Leaded and Lead-Free applications)

Flux Classification: ROL1
Specific Gravity: 0.9
Packaging: 10ml Pen

Shelf Life: Refrigerated >24 months, Unrefrigerated >24 months

## **Dispensing**

Gently press tip into work piece (depress tip) to dispense.

## Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). The liquid flux can be allowed to freeze. Freezing will not degrade this product. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

#### **Transportation**

This product requires ground shipping. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground will not impact this product's stated shelf life.

#### Cleaning

This is a water-soluble liquid flux; post-use cleaning is required. Clean with water or isopropyl alcohol (IPA).

### **Conforms to the following Industry Standards:**

J-STD-004B, Amendment 1 (Solder Fluxes):

Yes

RoHS 3 Directive 2015/863/EU:

Yes