




1

MDCD33-12-10-A

Ruland MDCD33-12-10-A, 12mm x 10mm Double Disc Coupling, Aluminum, Clamp Style, 33.3mm OD, 45.0mm Length





Description

Ruland MDCD33-12-10-A is a clamp double disc coupling with 12mm x 10mm bores, 33.3mm OD, and 45.0mm length. It is zero-backlash and has a balanced design for reduced vibration at high speeds. The double disc design is comprised of two anodized aluminum hubs, two sets of thin stainless steel disc springs, and a center spacer allowing each disc to bend individually and accommodate all types of misalignment. MDCD33-12-10-A is lightweight and has low inertia making it well suited for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MDCD33-12-10-A to be torisionally rigid and an excellent fit for precise positioning stepper servo applications commonly found in semiconductor, solar, printing, machine tool, and test and measurement systems. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. MDCD33-12-10-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1) B1 Min Shaft Penetration B1 Max Shaft Penetration Outer Diameter (OD) Length (L) Recommended Shaft Tolerance Screw Material	12 mm 9.0 mm 21.4 mm 33.3 mm 45.0 mm +0.000 mm / -0.013 mm	Small Bore (B2) B2 Min Shaft Penetration B2 Max Shaft Penetration Bore Tolerance Hub Width (LH)	10 mm 9.0 mm 21.4 mm +0.03 mm / -0.00 mm
B1 Max Shaft Penetration Outer Diameter (OD) Length (L) Recommended Shaft Tolerance	21.4 mm 33.3 mm 45.0 mm +0.000 mm / -0.013 mm	B2 Max Shaft Penetration Bore Tolerance	21.4 mm +0.03 mm / -0.00 mm
Outer Diameter (OD) Length (L) Recommended Shaft Tolerance	33.3 mm 45.0 mm +0.000 mm / -0.013 mm	Bore Tolerance	+0.03 mm / -0.00 mm
Length (L) Recommended Shaft Tolerance	45.0 mm +0.000 mm / -0.013 mm		<u>, </u>
Recommended Shaft Tolerance	+0.000 mm / -0.013 mm	Hub Width (LH)	1= 0
			15.0 mm
Screw Material		Forged Clamp Screw	M3
oci cw iviateriai	Alloy Steel	Hex Wrench Size	2.5 mm
Screw Finish	Black Oxide	Seating Torque	2.1 Nm
Number of Screws	2 ea	Dynamic Torque Reversing	2.83 Nm
Angular Misalignment	2.0°	Dynamic Torque Non-Reversing	5.65 Nm
Parallel Misalignment	0.20 mm	Static Torque	11.3 Nm
Axial Motion	0.40 mm	Torsional Stiffness	28.6 Nm/Deg
Maximum Speed	10,000 RPM	Full Bearing Support Required?	Yes
Zero-Backlash?	Yes	Balanced Design	Yes
Forque Wrench	TW:BT-1R-1/4-18.3	Recommended Hex Key	Metric Hex Keys
Waterial Specification	Hubs and Center Spacer: 2024-T351 Aluminum Bar Disc Springs: Type 302 Stainless Steel	Temperature	-40°F to 200°F (-40°C to 93°C)
inish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize	Manufacturer	Ruland Manufacturing
Country of Origin	USA	Weight (lbs)	0.182100
JPC	634529084083	Tariff Code	8483.60.8000
JNSPC	31163008		
Note 1	Stainless steel hubs are available upon request.		
Note 2	Torque ratings are at maximum misalignment.		
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 4	Torque ratings for the couplings are based on the physical limitations/failure point of the disc springs. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the disc springs. In some case especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the disc springs. Keyways are available to provide additional torque capacity in		

the shaft/hub connection when required. Please consult technical support for more assistance.

Prop 65

MARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Installation Instructions

- 1. Align the bores of the MDCD33-12-10-A double disc coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (Angular Misialignment: 2.0°, Parallel Misalignment: 0.20 mm, Axial Motion: 0.40 mm)
- 2. Fully tighten the M3 screw on the first hub to the recommended seating torque of 2.1 Nm using a 2.5 mm hex torque wrench.
- 3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 21.4 mm.