Julabo

CORIO CP-BC6 Heating Circulator

In addition to the advantages of the CORIO C Circulator, the CORIO CD and CP Immersion Circulator can be equipped with an optional pump set for temperature control of external applications.

Your advantages

- Models for internal and external applications
- Bright, white, easy to read display
- Very quiet
- Easy switching between internal and external circulation
- Powerful and infinitely adjustable pressure pump
- USB connection
- RS232 interface for online communication
- $\boldsymbol{\cdot}$ High-quality bath tanks made of stainless steel with bath lid and drain tap
- Integrated pump connection M16×1
- Integrated cooling coil for counter-cooling
- Precise temperature control
- · Easy pump change-over between internal and external circulation



Technical data

Available voltage versions		Bath		
Order No.	9 013 506		Bath tank	Stainless steel
Available voltage versions:		Bath cover	integrated	
9 013 506.33	200-230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F)		Usable bath opening in. (W x L / D) $$	5.1 x 5.9 / 7.9
9 013 506.33.chn	200-230V/50-60Hz (CN Plug)			
9 013 506.04	200-230V/50-60Hz (UK Plug Type BS1363A) 200-230V/50-60Hz (CH Plug Type SEV 1011)			
9 013 506.05				
9 013 506.22	100-115V/50-60Hz	z (Nema N5-15 Plug)		
Other			Electronics	
Classification		Classification III (FL)	Temperature control	PID1
Pump function		Pressure Pump	Absolute temperature calibration	1 Point Calibration
Pump type		Immersion Pump	Temperature displayTemperature display	LED
			Temperature settingTemperature setting	Keypad
			Electronic Timer hr:min	0 999
Dimensions and volumes		Temperature values		
Weight Ibs		22	Working temperature range °C	+20 +200
Barbed fittings inner o	liameter	8/12 mm	Temperature stability °C	±0.02
Dimensions in. (W \times L	× H)	9.4 x 17.3 x 18.5	Ambient temperature °C	+5 +40
Filling volume I		4.5 6	Temperature display resolution °C	0.01 0.1
Fining volume i				

Performance values

Julabo

200-230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F)

200V/50Hz		200V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate l/min	8 27	Pump capacity flow rate l/min	8 27
Pump capacity flow pressure psi	1.5 10.2	Pump capacity flow pressure psi	1.5 10.2
230V/50Hz		230V/60Hz	
230V/50Hz Heating capacity kW	2	230V/60Hz Heating capacity kW	2
	2 50		2 50
Heating capacity kW	_	Heating capacity kW	_

200-230V/50-60Hz (CN Plug)

200V/50Hz		200V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate l/min	8 27	Pump capacity flow rate I/min	8 27
Pump capacity flow pressure psi	1.5 10.2	Pump capacity flow pressure psi	1.5 10.2
230V/50Hz		230V/60Hz	
230V/50Hz Heating capacity kW	2	230V/60Hz Heating capacity kW	2
	2 50		2 50
Heating capacity kW	_	Heating capacity kW	-

200-230V/50-60Hz (UK Plug Type BS1363A)

200V/50Hz		200V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate I/min	8 27	Pump capacity flow rate I/min	8 27
Pump capacity flow pressure psi	1.5 10.2	Pump capacity flow pressure psi	1.5 10.2
230V/50Hz		230V/60Hz	
230 1/ 30112		2307/0002	
Heating capacity kW	2	Heating capacity kW	2
	2 50		2 50
Heating capacity kW	_	Heating capacity kW	_

200-230V/50-60Hz (CH Plug Type SEV 1011)

200V/50Hz		200V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate I/min	8 27	Pump capacity flow rate l/min	8 27
Pump capacity flow pressure psi	1.5 10.2	Pump capacity flow pressure psi	1.5 10.2
230V/50Hz		230V/60Hz	

Julabo

Heating capacity kW	2	Heating capacity kW	2
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate I/min	8 27	Pump capacity flow rate I/min	8 27
Pump capacity flow pressure psi	1.5 10.2	Pump capacity flow pressure psi	1.5 10.2

100-115V/50-60Hz (Nema N5-15 Plug)

100V/50Hz		100V/60Hz	
Heating capacity kW	0.8	Heating capacity kW	0.8
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate I/min	8 27	Pump capacity flow rate l/min	8 27
Pump capacity flow pressure psi	1.5 10.2	Pump capacity flow pressure psi	1.5 10.2
115V/50Hz		115V/60Hz	
Heating capacity kW	1	Heating capacity kW	1
Viscosity max. cST	50	Viscosity max. cST	50
Pump capacity flow rate I/min	8 27	Pump capacity flow rate l/min	8 27

All Benefits



ATC. Absolute Temperature Calibration, 1-point calibration (CD).



Handle with ease. Makes day-to-day work easy. Comfortably move your CORIO around by using the

ergonomic handles (front and rear).



Solid. Minimized energy loss through high-quality insulation.



Tidy. The special drain tap for easy draining of bath fluids without tools.




100% Checked. 100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.




Condensation protection.

Superb design solution. Integrated ventilation directs air over the bath lid and minimizes condensation.



Internal. External.





Stable.

Rubber feet allow for a secured footing of your CORIO to prevent damage to your laboratory equipment.



Touching permitted. Optimum safety. The ergonomic plastic handle protects your fingers from hot surfaces.



Green technology. Development consistently applied environmentally friendly materials and technologies.





JULABO. Quality. Highest standards of quality for a long product life.



Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Timer. Integrated.

CORIO circulators include an integrated timer function. When the set time has elapsed, a signal sounds and the device switches off. Setting range: 0 ... 999 minutes.



Brilliant.

Very bright display makes it easy to read even from a distance.



Exact.

You can rely on it. PID1 control and 'Active Cooling Control' make the new CORIO precise and perfect.



Switch on. And off you go. Intelligent operating concept. Ready for operation with just a few quick and easy steps.



Powerful. Adjustable. Strong pressure pump, continuously adjustable.



Connectivity. Remote control made easy. CORIO CP circulators feature a USB connection and RS232 interface.



Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



Connection. Easy.

Inclined pump connections (M16×1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



Everything at the front. All operating controls and safety functions are accessed easily and comfortably from the front.



Locked in. The lockable power plug guarantees safe connection. More process safety.



Early warning system for low liquid level Maximum safety for applications, optical and audible alarm, allows user to refill bath fluid before the unit shuts down



Early warning system for low liquid level. Maximum safety for your application. Optical and audible alarm allows user to refill bath fluid in time.